



# New, Improved Lens Maintenance Products from Honeywell Uvex

Fog Eliminator Plus Lens Cloths and Uvex Clear Plus Lens Cleaner

## Protecting Our Eyes and Protecting Our Investment

A few seconds without safety eyewear, removed to wipe off fog or dirt, can lead to serious injury. That's why investment in comfortable, stylish, proper fitting eyewear is so important. Protect your eyes and your investment with new and improved lens maintenance products from Honeywell Uvex.

### New Uvex Fog Eliminator Plus: it's clearly safe!

Uvex® Fog Eliminator Plus now delivers eight hours of anti-fog protection based on an extreme environment effectiveness (EEE) test at 122°F and 80% humidity for one hour. When applied, it's one of the longest lasting AF performance products in the market.. Fog Eliminator Plus Cloth and Gel on AF coating represents a minimum ~60X extension of the fog free time vs. AF coating alone!\*

Just a 10-second wipe bans fog caused by heat, cold, humidity, exertion or sudden temperature changes. The result is reliable, all-day protection from fog of any kind.

\* In laboratory tests# under extreme conditions (≥40C (104F) and ≥80%RH)



### Available in Uvex Fog Eliminator Plus Cloths and new Uvex Fog Eliminator Plus Gel for convenient, drip-free application

#### Benefits of Uvex Fog Eliminator Plus Cloth and Gel

- Delivers 8-hour fog protection; AF properties can last up to 1 week undisturbed
- Protects lenses from fogging and frosting at colder than -18°C (0°F)
- Safe for all lens surfaces – including polycarbonate, glass, coated and mirrored
- Non-flammable and non-toxic

- Delivers static-free, streak-free, and film-free optical clarity
- Silicone and alcohol-free\* including butoxyethanol-free
- Pleasant smell is from all natural papaya extract
- 3-5 year shelf life
- Made in the U.S.A.

\* Methanol, ethanol, and isopropanol-free

\*\* Less than 2% by weight



### NEW! Uvex Fog Eliminator Plus Anti-Fog Gel 6pk Bottles

- Delivers all the industry-leading benefits of Uvex Fog Eliminator Plus Cloths in a gel for easy drip-free, mess-free application
- One 10ml bottle lasts up to 300 applications
- Apply using any non-linting tissue or microfiber cloth
- Dropper bottles offer convenience and portability

#### S479 – Uvex Fog Eliminator Plus Cloths

5.25"W x 2.25"L x 8"H

100 individually-wrapped cloths/box

#### S481 – Uvex Fog Eliminator Plus Anti-Fog Gel 6pk

3.06"W x 2"L x 3"H per 6pk

Six (6) 10 ml dropper bottles/box





**Uvex Clear® Plus Cleaners work even harder with this NEW, IMPROVED, PROPRIETARY formula!**

From the experts in lens technology comes a lens cleaner that swiftly lifts and removes tough dirt, debris and even oily fingerprints to restore optical clarity. Uvex Clear® Plus Lens Cleaner reduces visible soil to below detectable limits leaving no haze, streaks or residue behind. It also has a pleasant smell and it's toxic-free!

Our improved formula delivers safe, effective results in an isopropanol- and silicone-free solution that won't damage or delaminate lenses. Simply wipe soiled lenses with the solution for 10 seconds and let dry for an easy-to-achieve, long-lasting clean.

- Swiftly lifts and removes dirt, dust, debris, oil
- Reduces visible soil to below detectable limits (.2 to .3% haze)
- Streak-free, residue-free, haze-free results
- Alcohol and silicone-free
- Methanol, ethanol, and isopropanol-free
- Butoxyethanol-free
- Pleasant smell from all natural papaya extract
- Safe to use on any lens or coated surface
- Won't degrade or delaminate lens material
- Can be used in temps as low as -40°C (-40°F)
- Proprietary formula
- 3-5 year shelf life
- Made in the U.S.A.



**S474 - Uvex Clear Plus Lens Tissue**  
4.72"W x 7.87"L x 2.09"H

Elegant, non-abrasive, THICKER, soft cloth dry tissue for use with lens cleaning solution products (500/box)

**S471 - Uvex Clear Plus Lens Cleaner Solution**  
1.95"W x 3"L x 10.25"H

Refillable 16 oz. spray bottle

**S482 - Uvex Clear Plus Lens Cleaner Refill Solution**  
12.25"W x 12.25"L x 12.75"H

1-gallon refill bottle

**S470 - Uvex Clear Plus Towelettes**  
5.25"W x 2.25"L x 8"H

Pre-moistened, pocket-sized and convenient for use on the go (100/box)

**S484 - Uvex Clear Plus Permanent Lens Cleaning Station**  
30"W x 4"L x 14"H



One (1) 16 oz. bottle of Uvex Clear Plus cleaning solution, 4 boxes of 500 tissues and a 3.5" x 4.5" mirror

**S483 - Uvex Clear Plus Portable, Disposable Lens Cleaning Station**  
16"W x 3.19"L x 9.25"H

Holds 16 oz. of Uvex Clear Plus cleaning spray and 1,500 tissues



# How-to Guide **Anti-Fog Cloths and Gel**

## **3 steps to using** Uvex Fog Eliminator Plus Anti-Fog Cloths and Gel



<p>1</p>  <p>Wipe lenses clean</p>	<p>2</p>  <p>With Uvex Fog Eliminator Plus Cloth: Rub Uvex Fog Eliminator Plus cloth on lenses in circular motion for 10 seconds</p> <p>With Uvex Fog Eliminator Plus Gel: Apply less than a drop of Uvex Fog Eliminator Plus to each lens, using a non-lint tissue or microfiber cloth, rub in circular fashion until an even coating is applied to each lens</p>	<p>3</p>  <p>With Uvex Fog Eliminator Plus AF Cloth: Let lenses dry thoroughly</p> <p>With Uvex Fog Eliminator Plus AF Gel: Rub gently like a polish until it's clear; no dry time needed</p>
---	---	---

# How-to Guide **Lens Cleaners**

## **2 steps to clean lenses with** Uvex Clear Plus Lens Cleaner Cloths

<p>1</p>  <p>Rub pre-moistened Uvex Clear Plus cloth on lenses in circular motion until soil is removed</p>	<p>2</p>  <p>Let lenses dry</p>
--	--

## **2 steps to clean lenses with** Uvex Clear Plus Spray

<p>1</p>  <p>Apply 1 spray of cleaner onto each lens</p>	<p>2</p>  <p>Using Uvex Clear Plus lint-free tissue or microfiber cloth, rub cleaner onto lenses until soil is removed</p>
--	---

### **Honeywell Industrial Safety**

9680 Old Bailes Rd,  
Fort Mill, SC 29707  
US:  
Tel. 800.430.5490  
Fax. 800.322.1330  
www.honeywell.com

Canada:  
Tel. 888.212.7233  
Fax. 888.667.8477

Uvex is a registered trademark of Honeywell International Inc.  
HIS\_Uvex Lens Maintenance-FLR-EN | Rev A | 05/19  
©2019 Honeywell International Inc.

**Honeywell**