
Mitutoyo

Toolmakers' Microscopes TM Series



Mitutoyo

Bright and Clear Field of View. Best Performance in **Small-model Class.**

FEATURES

 Newly designed LED illuminators provide enhanced observation for higher accuracy and resolution.



Conventional illumination



Newly designed LED illumination



Optional LED circular illuminator available for applications requiring all-round lighting.

176-208A



A vernier scale mounted outside the eyepiece enables simple angle measurement.

Optional Accessories

Eyepieces and Objectives see page 4

Digital Imaging with Software

Order No.	Description
64AAB429	MOTICAM 2, 2.0 MEGAPIXEL-1/3" CMOS, USB
64AAB430	MOTICAM 3, 3.0 MEGAPIXEL-1/2" CMOS, USB
64AAB431	MOTICAM 5, 5.0 MEGAPIXEL-1/2.5" CMOS, USB
64AAB432	MOTICAM 580, 5.0 MEGAPIXEL-1/2.3" CMOS, USB/HDMI
64PMI237	MOTICAM EYETUBE ADAPTOR



LED ring light 64AAB214



Digimatic Micrometer Heads (LCD readout)




SPECIFICATIONS


Model No.		TM-505B	TM-A505B	TM-1005B	TM-A1005B		
Order No.		176-818A	176-820A	176-819A	176-821A		
Optical tube		Monocular type (Vertical tilt angle: 60°)					
Observation image		Erect					
Eyepiece protractor		Resolution (graduation): 1°, Rotation angle: 360°, Resolution (angle): 6', Adjustable zero point					
Eyepiece		Standard accessory: 15X (field number: 13), Options: 10X, 20X					
Objective lens		Standard accessory: 2X, Options: 5X, 10X					
Microscope head	Maximum height of workpiece	4.53" /	115mm	4.21" / 107mm			
	Focusing method	Manual (Coarse feed)					
Illumination	Transmitted illumination	Stepless brightness adjustment, White LED light source, With green filter					
unit	Surface illumination	Oblique	t source				
Cross-travel stage	Measuring range	2" x 2" /	50×50mm	4" x 2" / 100×50mm (An optional 2"/50mm gauge block is required to cover full range. A CERA block is recommended.)			
	Table size	16" x 6" /	52×152mm	9.44" x 6" / 240×152mm			
	Usable area of the stage glass	3.8" x 3.8"	/96×96mm	6" x 3.8" / 154×96mm			
	Maximum stage glass loading	11 lbs. / 5kg					
Linear measurement method		Micrometer heads optional	Micrometer heads included	Micrometer heads optional	Micrometer heads included		
Resolution		N/A	.00005"/1µm	N/A	.00005 "/1μm		
Micrometer head travel range		N/A	N/A 2 "/50mm N/A		2 "/50mm		
Power supply		120VAC Maximum power consumption: 4.2W					
Main unit mass		31 lbs.	/ 14kg	33 lbs. / 15kg			



DIMENSIONS (including digital micrometer heads)



System configuration (accessories are optional)



Evepiece-Objective Performance Table


	Eyepiece 10X (176-115)			Eyepiece 15X (Standard accessory)			Eyepiece 20X (176-117)		
	Total magnification	Viewing field	Depth of focus	Total magnification	Viewing field	Depth of focus	Total magnification	Viewing field	Depth of focus
Objective 2X (Standard accessory)	20X	ø.256" (ø6.5mm)	158µm	30X	ø.256" (ø6.5mm)	124µm	40X	ø.197" (ø5mm)	107µm
Objective 5X (176-139)	50X	ø.102" (ø2.6mm)	56µm	75X	ø.102" (ø2.6mm)	47µm	100X	ø.079" (ø2mm)	42µm
Objective 10X (176-137)	100X	ø.051" (ø1.3mm)	24µm	150X	ø.051" (ø1.3mm)	21µm	200X	ø.039" (ø1mm)	19µm



















Magnification 10X Order No. 176-138³ 176-139 176-137 Numerical 0.07 0.14 aperture Working 2.638" 1 299' 551" distance (67mm) (33mm) (14mm) *Standard accessory

Coordinate Measuring Machines Optical Measuring Vision Measuring Systems Small Tool Instruments Digital Scale and DRO Systems Sensor Systems and Data Managemen

Whatever your challenges are, Mitutoyo supports you from start to finish.

Mitutoyo is not only a manufacturer of top-quality measuring products but one that also offers qualified support for the lifetime of the equipment, backed by comprehensive services that ensure your staff can make the very best use of the investment.

Mitutoyo offers product and metrology training, used in modern measuring technology. We can also measurement challenges in-house on a sub-contract



Find additional product literature and our product catalog

www.mitutoyo.com

Note: All information regarding our products, and in particular the illustrations, drawings, dimensional and performance data contained in this printed matter as well as other technical data are to be regarded as approximate average values. We therefore reserve the right to make changes to the corresponding designs. The stated standards, similar technical regulations, descriptions and illustrations of the products were valid at the time of printing. In addition, the latest applicable version of our General Trading Conditions will apply. Only quotations submitted by ourselves may be regarded as definitive. Specifications are subject to change without notice.

Mitutoyo products are subject to US Export Administration Regulations (EAR). Re-export or relocation of our products may require prior approval by an appropriate governing authority.

Trademarks and Registrations

Designations used by companies to distinguish their products are often claimed as trademarks. In all instances where Mitutoyo America Corporation is aware of a claim, the product names appear in initial capital or all capital letters. The appropriate companies should be contacted for more complete trademark and registration information.



Mitutoyo America Corporation

www.mitutovo.com One Number to Serve You Better 1-888-MITUTOYO (1-888-648-8869)

M³ Solution Centers:

Aurora, Illinois (Headquarters) Boston, Massachusetts Huntersville, North Carolina Mason, Ohio Plymouth, Michigan City of Industry, California Birmingham, Alabama Renton, Washington Houston, Texas

1.5M 0615-03 • Printed in USA • July 2015