

# MAGNIFIERS

## Tomahawk®

TKH10  
Clear

### TOMAHAWK MAGNIFIER-CLEAR

- TKH10 +1.0 diopter
- TKH15 +1.5 diopter
- TKH20 +2.0 diopter
- TKH25 +2.5 diopter



77H15  
Clear

## Tahoe®

### TAHOE MAGNIFIER-CLEAR

- 77H15 +1.5 diopter
- 77H20 +2.0 diopter



## Engineer®

61H15  
Clear

### 58MM ENGINEER MAGNIFIER-CLEAR

- 61H15 +1.5 diopter
- 61H20 +2.0 diopter
- 61H25 +2.5 diopter



1-800-955-6887 • [www.mcrcsafety.com](http://www.mcrcsafety.com)

JZWS 03/2012

# READ THE FINE PRINT MAGNIFIERS MAKE IT BIGGER



## Magnifier Safety Glasses – Focused on the Task at Hand

It's easy to lose sight of even the simplest tasks. Impaired vision can lead to costly downtime or accidents. That's why our safety glasses are built with magnifying lenses that exceed ANSI Z87+ standards. Plus, all of our magnifying glasses feature Duramass® scratch resistant coating and 99.9% UV protection.



# MAGNIFIERS

# MAGNIFIERS

## Bearkat®

Features include single wrap around lens with a universal nose bridge and hybrid temple design. Individually packaged in polybags and sold by the dozen.



### BEARKAT MAGNIFIER-CLEAR

- BKH10 +1.0 diopter
- BKH15 +1.5 diopter
- BKH20 +2.0 diopter
- BKH25 +2.5 diopter

BKH10 Clear



### BEARKAT MAGNIFIER-GRAY

- BKH10G +1.0 diopter
- BKH15G +1.5 diopter
- BKH20G +2.0 diopter
- BKH25G +2.5 diopter

BKH10G Gray



## Dallas®

Features include single wrap around lens with a lightweight frame, bayonet temple design, soft TPR nose pad, and full non-slip grip. Individually boxed and sold by the pair.



DLH10G Gray

### DALLAS® MAGNIFIER GRAY with Polished Black Frame

- DLH10G +1.0 diopter
- DLH15G +1.5 diopter
- DLH20G +2.0 diopter
- DLH25G +2.5 diopter



DLH10 Clear

### DALLAS® MAGNIFIER CLEAR with Polished Black Frame

- DLH10 +1.0 diopter
- DLH15 +1.5 diopter
- DLH20 +2.0 diopter
- DLH25 +2.5 diopter



K3H10 Clear

## Klondike®

Features include spatula temples designed to ratchet and extend for a customized fit, soft TPR nose pad, and lightweight polycarbonate lenses. Individually boxed and sold by the pair.

### KLONDIKE MAGNIFIER-CLEAR

- K3H10 +1.0 diopter
- K3H15 +1.5 diopter
- K3H20 +2.0 diopter
- K3H25 +2.5 diopter



K3H10G Gray

### KLONDIKE MAGNIFIER-GRAY

- K3H10G +1.0 diopter
- K3H15G +1.5 diopter
- K3H20G +2.0 diopter
- K3H25G +2.5 diopter



K3H10A Amber

### KLONDIKE MAGNIFIER-AMBER

- K3H10A +1.0 diopter
- K3H15A +1.5 diopter
- K3H20A +2.0 diopter
- K3H25A +2.5 diopter

## Klondike® RX



KDRX

**KDRX** Prescription insert for Klondike Plus (KD3) series frame options, which you can fill with your prescription at the prescription eyewear vendor of your choice.

## Determine Your Magnifier Diopter Strength

Determine the smallest text that you can read without glasses, with some difficulty, from a distance of 14 inches (average reading distance).	Diopter needed
We are MCR Safety... Just Try To Outwork Us!	+2.5
We are MCR Safety... Just Try To Outwork Us!	+2.0
We are MCR Safety... Just Try To Outwork Us!	+1.5
We are MCR Safety... Just Try To Outwork Us!	+1.0

\*\*Text size based on the Rosenbaum Optical Test Card viewed at 14 inches. The magnifying eyewear is designed to focus at a distance of 14 to 26 inches.